

Design that flexibly supports your best posture.

The union of style and comfort.The pliable frame harmonizes with your movementas the lumbar support comfortably contours the curves of your back. A design born of Okamura's fascination with ergonomics.

Portone



Function

з

There are Two Types of Portone According to Reclining Functions

Smart type

Standard type



comfortably accommodates

natural side-to-side movement.

■Adjustable Seat Height

pulling up the lever under the seat

120mr

Standard type

Adjust the height of the seat by

on the right

range : 120mm

Smart type

Adjustable Lumbar Support

The supple lumbar support fortifies your body's core, reinforcing a healthy posture.



The lumbar support easily adjusts to match your physical requirement. To adjust, simply grasp the lower ridge of the lumbar support and push up or down.




■Adjustable Seat Depth

Adjust the depth of the seat by operating the lever under the seat on the right (Smart type), left (Standard type) range

Smart type : 52mm /4 levels fixed Standard type : 55mm / 4 levels fixed 52mm [Smart type]






■Adjustable Arms (3D Arms)

The up and down [1D], angle [2D], back and forth [3D], positioning of the arm pads adjustable. The respective movable ranges are 62mm for up and down, 15 degrees for inside, 15 degrees for outside, 40mm for back and forth.



Headrest (Option)









Smart Fit Reclining Smart Type

The chair autematically adjusts the reclining tension in to a sitter's weight, regardless of each peason's unique physcai diffeerrences.



Reclining reaction force : Strong



Reclining reaction force : Weak

The backrest can be locked and released by operating the lever under the seat on the right (4 levels fixed)



Reclining Standard Type

• Reclining Tension Adjustment

Reclining tension can be adjusted by rotating the dial under the center of the seat. Turn clockwise to increase tension, or counterclockwise to reduce tension.


2 Lock and Release of Backrest

The backrest can be locked (in upright position only) by pushing in the lever under the seat on the light. To release, simply pull the lever out.



4

Back Colors



	Portone Smart	Portone Standard
	120mm	120mm
	4 levels fixed	4 levels fixed
	52mm	55mm
	4 levels fixed	fixed (Upright position only)
	19°	20°
n	Smart fit Reclining	Dial adjustment

окатига

OKAMURA CORPORATION International Sales & Marketing Div. www.okamura.com The products listed in this catalog are available as of January 2025. Please note that specifications, dimensions, and colors are subject to change without notice. The colors of the actual products may differ somewhat from the colors shown in the catalog, depending on printing conditions.